



WALL INSTALL TEMPLATE



DETAILS:



Hook-on Acrylic Holders for Photo Inserts

1. Acrylic holders are supported on horizontal rods mounted onto wall with **WM11** supports with 19 inches space on centers.

2. Join three of **R1500** rods to make the total length needed and cut to size. Rods are easily cut with a hacksaw to achieve the overall required length.

3. Use **REC** end caps for rod-end finishing if necessary, otherwise cut rods at support level.

4. Use **18HAP-SPACER** acrylic wall spacer to add back support to holders or dispensers.



**NOVADISPLAY**  
INNOVATIVE DISPLAY SOLUTIONS

Nova Display Systems, Inc.  
875 Wilson St., Ste. A-B  
Eugene, OR 97402  
541.505.7450  
541.505.9919 fax  
sales@novadisplay.com  
www.novadisplaysystems.com

Wall Display Concept

ID: **DC2613**

Title: Recognition Wall Display

Display Size:  
24"H x 173"W

Wall Size Requirements:  
16 FT (192 IN) Wide

Wall Install Template

ID: **DC2613-WT**

**Note:** Dimensions on the drawing display hardware mounting points on the wall. These are suggested dimensions and can be slightly modified to accommodate for your own wall specifics.

Note: This drawing is the property of Nova Display Systems and is not to be reproduced or copied in whole or in part. It is only to be used for the project and site specifically identified herein and is not to be used on any other projects, or for the purpose of manufacturing and reproduction. It is to be returned upon request.

Sheet: